



NKCR7.E300872
Auxiliary Devices Certified for Canada

If you notice a change to your NKCR7 Listing Card, click here to learn more.

Page Bottom

Auxiliary Devices Certified for Canada

See General Information for Auxiliary Devices Certified for Canada

PILZ GMBH & CO. KG
Felix-Wankel-Strasse 2
73760 Ostfildern, GERMANY

E300872

Investigated to CAN/CSA C22.2 No. 14-13

Auxiliary Device Enclosed Auxilliary Interface Module Model(s) PSEN sg1c-2/1, PSEN sg1c-2/1 2.2, PSEN sg1c-2/1 enabl, PSEN sg1c-4/1, PSEN sg1c-4/1 2.2, PSEN sg1c-4/1 enabl, PSEN sg1c-5/0

Auxiliary Device Enclosed Interlock Devices Model(s) PSEN ml 1.1 actuator, PSEN ml 2.1 actuator, PSEN ml b 1.1 switch, PSEN ml b 2.1 switch, PSEN ml b 2.2 switch, PSEN ml be 1.1 switch, PSEN ml be 2.1 switch, PSEN ml be 2.2 switch, PSEN ml s 1.1 switch, PSEN ml s 2.1 switch, PSEN ml s 2.2 switch, PSEN ml se 1.1 switch, PSEN ml se 2.1 switch, PSEN ml se 2.2 switch

Auxiliary Device Enclosed Listed for use with Auxilliary Interface Modules Model(s) PSEN sg1 actuator, PSEN sg1 actuator 2.2

Investigated to CAN/CSA C22.2. No. 14-10

Actuators, "Series Quartex-R" Model(s) 400539

Actuators Model(s) 400100, 400101, 400102, 400104, 400110, 400111, 400112, 400131, 400133, 400134, 400135, 400138, 400153, 400154, 400500, 400502, 400504, 400531, 400533, 400534, 400535, 400537, 400538, 400553, 400554, 400600, 400601, 400602

Auxiliary Device Open type Model(s) PSEN sl-0.5 1.1 - may be followed by additional suffixes

PSEN sl-0.5 2.1 - may be followed by additional suffixes

PSEN sl-0.5fm 1.1 - may be followed by additional suffixes

PSEN sl-0.5fm 2.1 - may be followed by additional suffixes

PSEN sl-0.5p 3.1, PSEN sl-0.5p 4.1, PSEN sl-0.5p 4.2, PSEN sl-0.5p 5.1, PSEN sl-0.5p 6.1, PSEN sl-0.5p 6.2

PSEN sl-1.0 1.1 - may be followed by additional suffixes

PSEN sl-1.0 2.1 - may be followed by additional suffixes

PSEN sl-1.0 VA - may be followed by additional suffixes

PSEN sl-1.0fm 1.1 - may be followed by additional suffixes

PSEN sl-1.0fm 2.1 - may be followed by additional suffixes

PSEN sl-1.0p 3.1, PSEN sl-1.0p 4.1, PSEN sl-1.0p 4.2, PSEN sl-1.0p 5.1, PSEN sl-1.0p 6.1, PSEN sl-1.0p 6.2

Auxiliary devices Model(s) PIT m2.1p DMG, may be followed by additional suffixes

PIT m2p DMG, may be followed by additional suffixes

PIT m2p, may be followed by additional suffixes

PIT m3.1p, may be followed by additional suffixes

PIT m3.2p, may be followed by additional suffixes

PIT m3.3p, may be followed by additional suffixes

PIT m3p , may be followed by additional suffixes

PSEN sl-0.5n 1.1, PSEN sl-0.5n 2.1, PSEN sl-0.5p 1.1, PSEN sl-0.5p 2.1, PSEN sl-0.5p 2.2, PSEN sl-1.0n 1.1, PSEN sl-1.0n 2.1, PSEN sl-1.0n 2.2, PSEN sl-1.0p 1.1, PSEN sl-1.0p 1.1VA, PSEN sl-1.0p 2.1, PSEN sl-1.0p 2.2, SEN sl-0.5n 2.2

Enclosures Model(s) 400200

Modular contact blocks Model(s) 400315, 400315\_V1

Investigated to CAN/CSA-C22.2 No.60947-1-13 and CAN/CSA C22.2 No.60947-5-1-14

Auxiliary Device Enclosed Model(s) PSEN sg2c-5CCLLE switch

Auxiliary Device Enclosed PSEN sg2c series Model(s) PSEN sg2c-3LPE switch, PSEN sg2c-3LBE switch, PSEN sg2c-3LPS switch, PSEN sg2c-3LBS switch, PSEN sg2c-3LPC switch, PSEN sg2c-3LBC switch, PSEN sg2c-3LPE 2.2 switch.

PSEN sg2c-5LPKLE-M12/5 switch, PSEN sg2c-5LBKLE-M12/5 switch, PSEN sg2c-5LPKLS-M12/5 switch, PSEN sg2c-5LBKLS-M12/5 switch, PSEN sg2c-5LPKLC-M12/5 switch, PSEN sg2c-5LBKLC-M12/5 switch, PSEN sg2c-5LPKLE-M12/5 2.2 switch.

PSEN sg2c-5LPLLE switch, PSEN sg2c-5LBLE switch, PSEN sg2c-5LPLLS switch, PSEN sg2c-5LBLLS switch, PSEN sg2c-5LPLLC switch, PSEN sg2c-5LBLLC switch, PSEN sg2c-5LPLLE 2.2 switch.

Auxiliary Devices Model(s) PIT gb LLE , PIT gb CLLE y, PIT gb BLE y, PIT gb KLE



Trademark and/or Tradename:

Last Updated on 2018-03-22

Questions?

Print this page

Terms of Use

Page Top

© 2018 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2018 UL LLC".